

LT elbow 45°



TECHNICAL DATA

Elbow brass nickel-plated conduit gland

Temperature range	-45°C to +105°C
Protection class	IP 67

■ STRUCTURE

- Material: Brass nickel plated
- Grounding sleeve: steel
- Sealing ring: Polyamide (PA)

■ PROPERTIES

- halogen-free

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- LIQUIDTIGHT gland for plastic-coated metallic protection tubes and high temperature protection tubes HTP. (An additional clamping ring is required).
The conical earthing sleeve offers maximum surface contact for optimum sealing and earthing.

■ NOTES

- Suitable for metallic protection tubes: EF, HTDL, OR, HC, HCX, ZHLS, HFX

metric thread

Part no.	Size	Suitable for tube ND	Suitable for tube outer Ø mm	Spanner size mm	Thread length mm	Packaging unit (in pc.)
94160	M16 x 1.50	3/8	17.8	26	13.0	10
94161	M20 x 1.50	1/2	21.1	29	13.0	10
94162	M25 x 1.50	3/4	26.4	35	15.0	5
94163	M32 x 1.50	1	33.1	45	15.0	5
920526	M40 x 1.50	1 1/4	41.8	54	16.0	2
920527	M50 x 1.50	1 1/2	47.8	63	18.0	2
920528	M63 x 1.50	2	59.9	77	20.0	2

PG thread

Part no.	Size	Suitable for tube ND	Suitable for tube outer Ø mm	Spanner size mm	Thread length mm	Packaging unit (in pc.)
91014	PG 11	3/8	17.8	26	12.0	10
91015	PG 13.5	3/8	17.8	26	12.0	10
91016	PG 16	1/2	21.1	29	13.0	10
91017	PG 21	3/4	26.4	35	15.0	5
91018	PG 29	1	33.1	45	15.0	5
91019	PG 36	1 1/4	41.8	54	16.0	2
91020	PG 42	1 1/2	47.8	63	16.0	2
91021	PG 48	2	59.9	77	18.0	2

LT elbow 45°



NPT thread

Part no.	Size	Suitable for tube ND	Suitable for tube outer Ø mm	Spanner size mm	Thread length mm	Packaging unit (in pc.)
905756	NPT 1/2"	3/8	17.8	26	12.0	10
905757	NPT 1/2"	1/2	21.1	29	13.0	10
905758	NPT 3/4"	3/4	26.4	35	15.0	5
905759	NPT 1"	1	33.1	45	15.0	5
905760	NPT 1 1/4"	1 1/4	49.0	54	16.0	2
905761	NPT 1 1/2"	1 1/2	61.0	63	18.0	2
905762	NPT 2"	2	66.0	77	20.0	2