


HSSV elbow 90° plastic



TECHNICAL DATA

Corrugated tubes conduit gland

Temperature range	-40°C to +110°C
Protection class	IP 65

■ STRUCTURE

- Material: Polyamide (PA) 6
- Flammability acc. to UL 94 (V0)

■ PROPERTIES

- halogen-free
- cadmium-free
- resistant to: fuels, mineral oils, greases, weak bases, weak acids

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- Quick-insert glands for a reliable, quick connection. Suitable for parallel-coiled HELUcond protection tubes.

■ NOTES

- UR-tested
- Protection classification: IP 66 with outer seal
- Threaded connection: metric to EN 60423
- Each unit includes 1 safety opener.

metric thread

Size	Suitable for nominal size	Thread length mm	Packaging unit (in pc.)	grey Part no.	black Part no.
M12 x 1.5	10	9.5	50	94200	94210
M16 x 1.5	10	9.0	50	98983	920190
M16 x 1.5	12	8.0	50	94201	94211
M20 x 1.5	16 / 17	10.5	50	94202	94212
M25 x 1.5	21 / 23	14.8	50	94203	94213
M32 x 1.5	29	13.8	25	94204	94214
M40 x 1.5	36 / 37	15.6	25	94205	94215
M50 x 1.5	48 / 50	16.0	10	94206	94216
M63 x 1.5	48 / 50	15.5	10	920191	920192

PG thread

Size	Suitable for nominal size	Thread length mm	Packaging unit (in pc.)	grey Part no.	black Part no.
PG 9	10	9.0	50	98440	98363
PG 11	12	7.7	50	98441	97382

Continued on next page

HSSV elbow 90° plastic



Size	Suitable for nominal size	Thread length mm	Packaging unit (in pc.)	grey	black
				Part no.	Part no.
PG 13.5	16 / 17	10.0	50	98442	98435
PG 16	16 / 17	10.0	50	98443	97944
PG 21	21 / 23	11.8	50	98444	98436
PG 29	29	11.5	25	98445	98437
PG 36	36 / 37	15.5	25	98446	98438
PG 48	48 / 50	16.0	10	98447	98439