


HSSV elbow 90° plastic



TECHNICAL DATA

corrugated tubes conduit gland

Temperature range -40°C to +110°C
Protection class IP 65

■ STRUCTURE

- Material: Polyamide (PA) 6
- Flammability acc. to UL 94 (V0)

■ PROPERTIES

- halogen-free
- cadmium-free
- resistant to: fuels, mineral oils, greases, weak bases, weak acids

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- Quick-insert glands for a reliable, quick connection. Suitable for parallel-coiled HELUcond protection tubes.

■ NOTES

- UR-tested
Protection classification: IP 66 with outer seal
Threaded connection: metric to EN 60423
Each unit includes 1 safety opener.

metric thread

Size	Suitable for nominal size	Thread length mm	Packaging unit (in pc.)	grey Part no.	black Part no.
M12 x 1.5	10.0	9.5	50	94200	94210
M16 x 1.5	10.0	9.0	50	98983	920190
M16 x 1.5	12.0	8.0	50	94201	94211
M20 x 1.5	16.0 / 17.0	10.5	50	94202	94212
M25 x 1.5	21.0 / 23.0	14.8	50	94203	94213
M32 x 1.5	29.0	13.8	25	94204	94214
M40 x 1.5	36.0 / 37.0	15.6	25	94205	94215
M50 x 1.5	48.0 / 50.0	16.0	10	94206	94216
M63 x 1.5	48.0 / 50.0	15.5	10	920191	920192

PG thread

Size	Suitable for nominal size	Thread length mm	Packaging unit (in pc.)	grey Part no.	black Part no.
PG 9	10.0	9.0	50	98440	98363
PG 11	12.0	7.7	50	98441	97382

Continued on next page

HSSV elbow 90° plastic

Size	Suitable for nominal size	Thread length mm	Packaging unit (in pc.)	grey	black
				Part no.	Part no.
PG 13.5	16.0 / 17.0	10.0	50	98442	98435
PG 16	16.0 / 17.0	10.0	50	98443	97944
PG 21	21.0 / 23.0	11.8	50	98444	98436
PG 29	29.0	11.5	25	98445	98437
PG 36	36.0 / 37.0	15.5	25	98446	98438
PG 48	48.0 / 50.0	16.0	10	98447	98439