

# T-SI



## TECHNICAL DATA

Silicone insulating tube acc. to DIN 40628

Temperature range -60°C to +200°C

### ■ STRUCTURE

- Material: Silicone

### ■ PROPERTIES

- softener free
- heavy metal free
- physiologically and toxicologically harmless
- with good chemical resistance

- weather-resistant
- ozone-resistant
- UV resistant

### ■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction
- for insulating
- bundling wires and lines

| Inner Ø mm | Wall thickness mm | Packaging unit (in m) | natural Part no. |
|------------|-------------------|-----------------------|------------------|
| 1.0        | 0.4               | 100                   | <b>94741</b>     |
| 2.0        | 0.4               | 100                   | <b>94742</b>     |
| 3.0        | 0.4               | 100                   | <b>97203</b>     |
| 4.0        | 0.5               | 100                   | <b>97426</b>     |
| 5.0        | 0.6               | 100                   | <b>97427</b>     |
| 6.0        | 0.6               | 100                   | <b>97757</b>     |
| 8.0        | 0.7               | 100                   | <b>94743</b>     |
| 10.0       | 0.7               | 50                    | <b>94744</b>     |
| 12.0       | 0.8               | 50                    | <b>94745</b>     |
| 14.0       | 0.8               | 50                    | <b>94746</b>     |
| 16.0       | 0.8               | 50                    | <b>94747</b>     |