

# T-SI



## TECHNICAL DATA

Silicone insulating tube acc. to DIN 40628

Temperature range -60°C to +200°C

- weather-resistant
- ozone-resistant
- UV resistant

## STRUCTURE

- Material: Silicone

## PROPERTIES

- softener free
- heavy metal free
- physiologically and toxicologically harmless
- with good chemical resistance

## APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology
- Control cabinet construction
- for insulating
- bundling wires and lines

Inner Ø mm	Wall thickness mm	Packaging unit (in m)	natural Part no.
1.0	0.4	100	<b>94741</b>
2.0	0.4	100	<b>94742</b>
3.0	0.4	100	<b>97203</b>
4.0	0.5	100	<b>97426</b>
5.0	0.6	100	<b>97427</b>
6.0	0.6	100	<b>97757</b>
8.0	0.7	100	<b>94743</b>
10.0	0.7	50	<b>94744</b>
12.0	0.8	50	<b>94745</b>
14.0	0.8	50	<b>94746</b>
16.0	0.8	50	<b>94747</b>