

# NSVM-S low voltage straight-through joint heat-shrinking type

multiple core



## NSVM-S (multi-core coupling sleeve)

Coupling sleeve for multi-core plastic-insulated power cables to 0.6/1 (1.2)kV, universal applications for connecting cables and lines from PVC, PE and VPE, e.g. N(A)YY, N(A)2XY, N(A)YCWY, NYM, NYY.

### Application

- Indoors
- Outdoors
- Underground
- Water

### Properties

- halogen-free
- high electrical insulation values
- laterally water-tight
- good mechanical strength
- compact dimensions
- unrestricted storage
- large line and cable cross-sections
- highly resistant to chemical influences, earth alkalis and UV rays

### Scope of delivery

- inner seal
- outer seal
- illustrated assembly instruction

### Test

According to CENELEC HD 623 (VDE0278, Part 623)

### multiple core

Part no.	Type	Nominal voltage U <sub>o</sub> /U(U <sub>m</sub> )	Cross-section mm <sup>2</sup>	Unit	Net EUR/item at a purchase of		
					1	2 - 5	6 - 10
94400	NSVM-S3	0.6/1kV	3x 1,5 - 3x 16,0	1	o. r.	o. r.	o. r.
94401	NSVM-S3	0.6/1kV	3x 6,0 - 3x 25,0	1	o. r.	o. r.	o. r.
94402	NSVM-S3	0.6/1kV	3x 25,0 - 3x 70,0	1	o. r.	o. r.	o. r.
94403	NSVM-S3	0.6/1kV	3x 95,0 - 3x 150,0	1	o. r.	o. r.	o. r.
94404	NSVM-S3	0.6/1kV	3x 185,0 - 3x 300,0	1	o. r.	o. r.	o. r.
93382	NSVM-S4	0.6/1kV	4x 1,5 - 4x 6,0	1	o. r.	o. r.	o. r.
93388	NSVM-S4	0.6/1kV	4x 1,5 - 4x 16,0	1	o. r.	o. r.	o. r.
93383	NSVM-S4	0.6/1kV	4x 6,0 - 4x 25,0	1	o. r.	o. r.	o. r.
93384	NSVM-S4	0.6/1kV	4x 16,0 - 4x 50,0	1	o. r.	o. r.	o. r.
93385	NSVM-S4	0.6/1kV	4x 25,0 - 4x 95,0	1	o. r.	o. r.	o. r.
93386	NSVM-S4	0.6/1kV	4x 25,0 - 4x 150,0	1	o. r.	o. r.	o. r.
93389	NSVM-S4	0.6/1kV	4x 95,0 - 4x 300,0	1	o. r.	o. r.	o. r.
94405	NSVM-S5	0.6/1kV	5x 1,5 - 5x 6,0	1	o. r.	o. r.	o. r.
94406	NSVM-S5	0.6/1kV	5x 1,5 - 5x 10,0	1	o. r.	o. r.	o. r.
94407	NSVM-S5	0.6/1kV	5x 1,5 - 5x 16,0	1	o. r.	o. r.	o. r.
94408	NSVM-S5	0.6/1kV	5x 16,0 - 5x 25,0	1	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request