

# Anaconda Sealite® HFX



## TECHNICAL DATA

Protection tube

Temperature range -55°C to +105°C  
short term up to +125°C

Protection class IP 67 / IP 66

## STRUCTURE

- Material: steel galvanized
- Outer sheath material: Polyurethan (PUR)
- reinforced, galvanised and spiral wound steel band
- with latched profile
- continuous cord seal
- extruded plastic sheath

## PROPERTIES

- resistant to: oil
- lead-free
- low smoke development
- low toxicity in case of fire
- flexible at low temperatures

## APPLICATION

- Railway technology
- Tunnels
- Vehicle construction and shipbuilding
- public buildings
- Due to the complex construction method, the plastic sheath and internal tube flush together.

## NOTES

- Suitable connection glands:  
CV Compact straight, CV Compact elbow 45° and 90°

trade size inch	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	black Part no.
5/16	10.1	14.4	30	<b>94994</b>
3/8	12.6	17.8	30	<b>94995</b>
1/2	16.0	21.1	30	<b>94996</b>
3/4	21.0	26.4	30	<b>94997</b>
1	26.5	33.1	30	<b>94998</b>
1 1/4	35.1	41.8	30	<b>94999</b>