

KVA-CCSP



TECHNICAL DATA

PVC sealing insert

Temperature range -20°C to +105°C

■ STRUCTURE

- Material: Soft PVC

■ APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- For use with KVA gland bodies.

Part no.	Size	Size	Sealing insert colour	Cable Ø from / to mm	Packaging unit (in pc.)
96005	PG 7		yellow	4.0 - 6.5	100
90299		M12 x 1.5	yellow	4.0 - 6.5	100
96006	PG 9	M16 x 1.5	yellow	4.0 - 6.5	100
96007	PG 9	M16 x 1.5	grey	5.0 - 8.0	100
96008	PG 9	M16 x 1.5	black	6.5 - 9.5	100
96387	PG 11	M20 x 1.5	yellow	4.0 - 6.5	100
96389	PG 13.5	M20 x 1.5	yellow	4.0 - 6.5	100
96009	PG 11	M20 x 1.5	grey	5.0 - 8.0	100
96388	PG 13.5	M20 x 1.5	grey	5.0 - 8.0	100
96010	PG 11	M20 x 1.5	black	6.5 - 9.5	100
96012	PG 13.5	M20 x 1.5	black	6.5 - 9.5	100
96011	PG 11	M20 x 1.5	green	7.0 - 10.5	100
96013	PG 13.5	M20 x 1.5	green	7.0 - 10.5	100
96014	PG 13.5	M20 x 1.5	red	9.0 - 13.0	100
96391	PG 16	M25 x 1.5	yellow	4.0 - 6.5	50
96390	PG 16	M25 x 1.5	grey	5.0 - 8.0	50
96016	PG 16	M25 x 1.5	black	6.5 - 9.5	50

Part no.	Size	Size	Sealing insert colour	Cable Ø from / to mm	Packaging unit (in pc.)
96017	PG 16	M25 x 1.5	green	7.0 - 10.5	50
96018	PG 16	M25 x 1.5	red	9.0 - 13.0	50
96019	PG 16	M25 x 1.5	white	11.5 - 15.5	50
96020	PG 21	M32 x 1.5	green	7.0 - 10.5	50
96021	PG 21	M32 x 1.5	red	9.0 - 13.0	50
96022	PG 21	M32 x 1.5	white	11.5 - 15.5	50
96023	PG 21	M32 x 1.5	blue	14.0 - 18.0	50
96024	PG 21	M32 x 1.5	brown	17.0 - 21.0	50
96025	PG 29	M40 x 1.5	blue	14.0 - 18.0	25
96026	PG 29	M40 x 1.5	brown	17.0 - 21.0	25
96027	PG 29	M40 x 1.5	orange	20.0 - 25.0	25
96393	PG 29	M40 x 1.5	light yellow	24.0 - 28.0	25
96028	PG 36	M50 x 1.5	anthracite	27.0 - 32.0	25
96029	PG 36	M50 x 1.5	light blue	29.0 - 34.0	25
96030	PG 36	M50 x 1.5	pink	32.0 - 37.0	25
96031	PG 42	M50 x 1.5	white	36.0 - 41.0	10