

Anaconda Sealtite® HCX



TECHNICAL DATA

Protection tube

Temperature range -55°C to +145°C
short term up to +160°C

Protection class IP 67

- extruded plastic sheath

APPLICATION

- For extensive temperature ranges.
Due to the complex construction method, the plastic sheath and internal tube flush together.

STRUCTURE

- Material: steel galvanized
- reinforced, galvanised and spiral wound steel band
- with latched profile
- continuous cord seal

NOTES

- Suitable connection glands:
LT-straight, LT-elbow 45° and 90°
CV Compact straight, CV Compact elbow 45° and 90°

trade size inch	Inner Ø mm	Outer Ø mm, approx.	Packaging unit (in m)	black Part no.
3/8	12.6	17.8	30	94735
1/2	16.0	21.1	30	96410
3/4	21.0	26.4	30	96954
1	26.5	33.1	30	97945
1 1/4	35.1	41.8	15	96247
1 1/2	40.3	47.8	15	97668
2	51.6	59.9	15	97811