



TECHNICAL DATA

Spiral wound metallic tube acc. to DIN EN IEC 61386-23

Temperature range -50°C to +250°C
 Protection class IP 40

■ STRUCTURE

- Material: Cold strip acc. to EN 10139 DC 03, Fe/ Zn 3, galvanized
- with double-folded profile (Agraff profile)

■ PROPERTIES

- high tensile and torsional strength.

■ APPLICATION

- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction

■ NOTES

- Suitable connection glands: MTG-US, MTG-LI

Part no.	Inner Ø mm	Outer Ø mm, approx.	Weight kg, approx.	Packaging unit (in m)
97014	8.0	10.0	0.09	50.0
97015	12.0	14.0	0.155	50.0
97016	14.0	17.0	0.24	50.0
97017	16.0	19.0	0.29	50.0
97018	18.0	21.0	0.29	50.0

Part no.	Inner Ø mm	Outer Ø mm, approx.	Weight kg, approx.	Packaging unit (in m)
97019	24.0	27.0	0.38	50.0
97020	31.0	36.0	0.64	25.0
97021	40.0	45.0	0.84	25.0
97022	51.0	56.0	1.10	25.0