



TECHNICAL DATA

CR cuttable sealing ring

Temperature range -30°C to +120°C

■ STRUCTURE

- Material: Chloroprene rubber (CR)

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- For universal cable inlet through large cable clamping areas.

■ APPLICATION

■ NOTES

- Incision sealing rings for PG thread:
Material: Natural rubber
Temperature range: -40°C up to 90°C
- Legend:
Dimensions
D - Outer diameter
d - Inner diameter
S - Strength

metric thread

Part no.	Size	Inner Ø mm	Outer Ø mm, approx.	incisions mm	Thickness mm	Packaging unit (in pc.)
94860	M12 x 1.5	5	10.7		5	100
94861	M16 x 1.5	3	13.8	5.5 / 9.0	5.5	100
94863	M20 x 1.5	4	17.7	7.0 / 10.0 / 13.0	6	100
94865	M25 x 1.5	8.5	22.5	11.0 / 14.0 / 17.0	8	100
94866	M32 x 1.5	16	29.5	19.0 / 21.0 / 24.0	9.5	100
94867	M40 x 1.5	23	37.5	26.0 / 29.0 / 32.0	11	100
94868	M50 x 1.5	32	47.5	35.0 / 38.0 / 41.0	12	100
94869	M63 x 1.5	41	60.3	44.0 / 47.0 / 50.0	14	100

PG thread

Part no.	Size	Inner Ø mm	Outer Ø mm, approx.	incisions mm	Thickness mm	Packaging unit (in pc.)
96357	PG 9	5	13.3	7.5 / 10.0	5.5	100
96358	PG 11	7.5	16.5	10.0 / 12.5	6	100
96359	PG 13.5	7.5	18.3	10.0 / 12.5	6	100
96360	PG 16	7.5	20.4	10.0 / 12.5 / 15.0	7	100
96361	PG 21	10	25.9	13.0 / 16.0 / 19.0	8	100
96362	PG 29	18	34.7	21.0 / 24.0 / 27.0	9.5	100
96363	PG 36	24	44.7	27.0 / 30.0 / 33.0	12	100
96364	PG 42	30	51.7	33.0 / 36.0 / 39.0	14	100
96365	PG 48	36	56.9	39.0 / 42.0 / 45.0	14	100