



TECHNICAL DATA

Spiral wound metallic tube

Temperature range -50°C to +250°C
 short term up to +220°C

Protection class IP 40

■ STRUCTURE

- Material: Cold strip acc. to DIN 1624 St 2, Fe/ Zn 3, galvanized
- with latched profile

■ PROPERTIES

- high tensile and transverse pressure load rating
- high flexible

■ APPLICATION

- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction

■ NOTES

- Suitable connection glands: MTG-US, MTG-LI

| Part no. | Inner Ø mm | Weight kg, approx. | Outer Ø mm, approx. | Packaging unit (in m) |
|----------|------------|--------------------|---------------------|-----------------------|
| 97023 | 8.0 | 0.05 | 10.0 | 50 |
| 97024 | 11.0 | 0.12 | 14.0 | 50 |
| 97025 | 14.0 | 0.14 | 17.0 | 50 |
| 97026 | 16.0 | 0.15 | 19.0 | 50 |
| 97027 | 18.0 | 0.21 | 21.0 | 50 |

| Part no. | Inner Ø mm | Weight kg, approx. | Outer Ø mm, approx. | Packaging unit (in m) |
|----------|------------|--------------------|---------------------|-----------------------|
| 97028 | 23.0 | 0.26 | 27.0 | 50 |
| 97029 | 31.0 | 0.48 | 36.0 | 25 |
| 97030 | 40.0 | 0.62 | 45.0 | 25 |
| 97031 | 51.0 | 0.80 | 56.0 | 25 |

small pack

| Part no. | Inner Ø mm | Weight kg, approx. | Outer Ø mm, approx. | Packaging unit (in m) |
|----------|------------|--------------------|---------------------|-----------------------|
| 94880 | 8.0 | 0.05 | 10.0 | 10 |
| 94881 | 11.0 | 0.12 | 14.0 | 10 |
| 94882 | 14.0 | 0.14 | 17.0 | 10 |
| 94883 | 16.0 | 0.15 | 19.0 | 10 |
| 94884 | 18.0 | 0.21 | 21.0 | 10 |

| Part no. | Inner Ø mm | Weight kg, approx. | Outer Ø mm, approx. | Packaging unit (in m) |
|----------|------------|--------------------|---------------------|-----------------------|
| 94885 | 23.0 | 0.26 | 27.0 | 10 |
| 94886 | 31.0 | 0.48 | 36.0 | 10 |
| 94887 | 40.0 | 0.62 | 45.0 | 10 |
| 94888 | 51.0 | 0.80 | 56.0 | 10 |