

USK



TECHNICAL DATA

PP-tube connector

Temperature range -10°C to +110°C
Protection class IP 54

STRUCTURE

- Material: Polypropylene (PP)

APPLICATION

- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction
- Tube gland for type PT-S, S-PU and Airflex-K protection tubes. With high degree of protection.

metric thread

Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)	grey Part no.
M10 x 1.00	10.0	10.0	50	97594
M12 x 1.50	14.0	12.0	50	97595
M16 x 1.50	17.0	12.0	50	97596
M20 x 1.50	21.0	13.0	50	97597
M25 x 1.50	27.0	13.0	25	97598
M32 x 1.50	36.0	15.0	25	97599
M40 x 1.50	45.0	15.0	25	97600
M50 x 1.50	56.0	16.0	10	97601

metric thread - small packages

Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)	grey Part no.
M10 x 1.00	10.0	10.0	10	93460
M12 x 1.50	14.0	12.0	10	93461
M16 x 1.50	17.0	12.0	10	93462
M20 x 1.50	21.0	13.0	10	93463
M25 x 1.50	27.0	13.0	10	93464
M32 x 1.50	36.0	15.0	2	93465
M40 x 1.50	45.0	15.0	2	93466
M50 x 1.50	56.0	16.0	2	93467

USK

PG thread

Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)	grey Part no.
PG 7	10.0	10.0	50	90664
PG 9	14.0	10.0	50	90665
PG 11	17.0	10.0	50	90666
PG 13.5	19.0	10.0	50	90667
PG 16	21.0	11.0	50	90668
PG 21	27.0	11.0	25	90669
PG 29	36.0	12.0	25	90670
PG 36	45.0	12.0	25	90671
PG 48	56.0	15.0	10	90673

PG thread - small packages

Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)	grey Part no.
PG 7	10.0	10.0	10	93450
PG 9	14.0	10.0	10	93451
PG 11	17.0	10.0	10	93452
PG 13.5	19.0	10.0	10	93453
PG 16	21.0	11.0	10	93454
PG 21	27.0	11.0	10	93455
PG 29	36.0	12.0	2	93456
PG 36	45.0	12.0	2	93457
PG 48	56.0	15.0	2	93458