

LK-I



TECHNICAL DATA

PP-tube connector

Temperature range -10°C to +110°C
Protection class IP 54

• Material: Polypropylene (PP)

■ APPLICATION

- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction
- Tube gland for protection tubes type PT-S, S-PU and Airflex-K.

■ STRUCTURE

metric thread

Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)	grey Part no.
M12 x 1.5	10.0	10.0	50	97602
M16 x 1.5	14.0	10.0	50	97603
M20 x 1.5	17.0	10.0	50	97604
M25 x 1.5	21.0	11.0	50	97605
M32 x 1.5	27.0	12.0	25	97606
M40 x 1.5	36.0	12.0	25	97607
M50 x 1.5	45.0	12.0	25	97608
M63 x 1.5	56.0	15.0	10	97609

metric thread - small packages

Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)	grey Part no.
M12 x 1.5	10.0	10.0	10	93480
M16 x 1.5	14.0	10.0	10	93481
M20 x 1.5	17.0	10.0	10	93482
M25 x 1.5	21.0	11.0	10	93483
M32 x 1.5	27.0	12.0	10	93484
M40 x 1.5	36.0	12.0	2	93485
M50 x 1.5	45.0	12.0	2	93486
M63 x 1.5	56.0	15.0	2	93487

LK-I

PG thread

Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)	grey Part no.
PG 7	10.0	10.0	50	90720
PG 9	14.0	10.0	50	90721
PG 11	17.0	10.0	50	90722
PG 13.5	19.0	10.0	50	90723
PG 16	21.0	11.0	50	90724
PG 21	27.0	11.0	25	90725
PG 29	36.0	12.0	25	90726
PG 36	45.0	12.0	25	90727
PG 48	56.0	15.0	10	90729

PG thread - small packages

Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)	grey Part no.
PG 7	10.0	10.0	10	93470
PG 9	14.0	10.0	10	93471
PG 11	17.0	10.0	10	93472
PG 13.5	19.0	10.0	10	93473
PG 16	21.0	11.0	10	93474
PG 21	27.0	11.0	10	93475
PG 29	36.0	12.0	2	93476
PG 36	45.0	12.0	2	93477
PG 48	56.0	15.0	2	93478