


HSK-MS-E-D



TECHNICAL DATA

Nickel plated brass EMC cable gland

Temperature range -40°C to +100°C
Protection class IP 68 - 10 bar / IP 69K

STRUCTURE

- Material: Brass, nickel plated
- Clamp: Polyamide (PA) metal-plated
- Seal: Nitrile butadiene rubber (NBR)
- O-ring: Nitrile butadiene rubber (NBR)

PROPERTIES

- optimum strain relief through clamping lamella
- easy to assemble, time and cost savings
- watertight, dust-tight
- large clamping areas

APPLICATION

- Machine and plant construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction
- To meet stringent requirements in technology. Time-saving and simple handling through metallised terminal insert, which is automatically contacted when the gland is closed.

NOTES

- Legend:
Dimensions
TD - Thread Diameter
TL - Thread Length
SZ - Spanner Size

metric thread

Part no.	Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
98055	M12 x 1.5	3.0 - 6.5	6.5	14	50
98056	M16 x 1.5	5.0 - 10.0	6.0	20	50
98057	M20 x 1.5	10.0 - 14.0	6.0	24	50
98058	M25 x 1.5	13.0 - 18.0	7.0	30	25
98059	M32 x 1.5	18.0 - 25.0	8.0	40	25
98060	M40 x 1.5	24.0 - 32.0	8.0	50	10
90160	M50 x 1.5	32.0 - 38.0	9.0	64	5
90161	M63 x 1.5	37.0 - 44.0	10.0	64 / 68	5

PG thread

Part no.	Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
97655	PG 7	3.0 - 6.5	5.0	14	50
97656	PG 9	4.0 - 8.0	6.0	17	50
97657	PG 11	5.0 - 10.0	6.0	20	50
97658	PG 13.5	6.0 - 12.0	6.5	22	50
97659	PG 16	10.0 - 14.0	6.5	24	50
97660	PG 21	13.0 - 18.0	7.0	30	25

Continued on next page

HSK-MS-E-D



Part no.	Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
97752	PG 29	18.0 - 25.0	8.0	40	25
97788	PG 36	24.0 - 32.0	8.0	50	10