


HSK-MZ-E



TECHNICAL DATA

Nickel plated brass EMC cable gland

Temperature range -40°C to +100°C
Protection class IP 68 - 10 bar / IP 69K

■ STRUCTURE

- Material: Brass, nickel plated
- Clamp: Polyamide (PA)
- Seal: Nitrile butadiene rubber (NBR)
- O-ring: Nitrile butadiene rubber (NBR)
- with double bracket strain relief

■ PROPERTIES

- optimum strain relief through clamping lamella
- easy to assemble, time and cost savings

- watertight, dust-tight
- large clamping areas

■ TESTS

- Test standard EN 62444

■ APPLICATION

- Machine and plant construction
- Automation technology
- Vehicle construction and shipbuilding
- Installation technology

■ NOTES

- Legend:
Dimensions
TD - Thread Diameter
TL - Thread Length
SZ - Spanner Size

metric thread

Part no.	Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
98070	M12 x 1.5	3.0 - 6.5	6.5	14	50
98071	M16 x 1.5	5.0 - 10.0	6.0	20	50
98072	M20 x 1.5	10.0 - 14.0	6.0	24	50
98073	M25 x 1.5	13.0 - 18.0	7.0	30	25
98074	M32 x 1.5	18.0 - 25.0	8.0	40	25
98075	M40 x 1.5	22.0 - 32.0	8.0	50	10
90162	M50 x 1.5	32.0 - 38.0	9.0	57	5
90163	M63 x 1.5	37.0 - 44.0	10.0	64 / 68	5

PG thread

Part no.	Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
98061	PG 7	3.0 - 6.5	5.0	14	50
98062	PG 9	4.0 - 8.0	6.0	17	50
98063	PG 11	5.0 - 10.0	6.0	20	50
98064	PG 13.5	6.0 - 12.0	6.5	22	50
98065	PG 16	10.0 - 14.0	6.5	24	50

Continued on next page

HSK-MZ-E



Part no.	Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
98201	PG 21	13.0 - 18.0	7.0	30	25
98066	PG 29	18.0 - 25.0	8.0	40	25
98067	PG 36	22.0 - 32.0	8.0	50	10
98068	PG 42	32.0 - 38.0	9.0	57	5
98069	PG 48	37.0 - 44.0	10.0	64	5

NPT thread

Part no.	Size	Cable Ø from / to mm	Thread length mm	Spanner size mm	Packaging unit (in pc.)
92908	NPT 3/8"	4.0 - 8.0	15.0	17 / 19	50
92909	NPT 1/2"	6.0 - 12.0	13.0	22 / 24	50
92910	NPT 3/4"	13.0 - 18.0	13.0	30	25