



TECHNICAL DATA

Metal-tube gland

Temperature range	-40°C to +250°C
Protection class	IP 40

■ STRUCTURE

- Material: Brass nickel plated
- Grounding sleeve: Brass bare

- Retaining ring: spring steel

■ APPLICATION

- Tube gland for protection tubes type S, S-PU, M, SPR-AS, SPR-EDU-AS, SPR-PVC-AS.
The rotating interior sockets with tube rotation lock is inserted into the gland and secured against tearing by the spring steel ring.

metric thread

Part no.	Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)
97619	M10 x 1.00	10.0	10.0	50
97620	M12 x 1.50	14.0	10.0	50
97621	M16 x 1.50	17.0	10.0	50
97622	M20 x 1.50	21.0	10.0	50

Part no.	Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)
97623	M25 x 1.50	27.0	11.0	25
97624	M32 x 1.50	36.0	13.0	25
97625	M40 x 1.50	45.0	13.0	25
97626	M50 x 1.50	56.0	14.0	10

metric thread - small packages

Part no.	Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)
93610	M10 x 1.00	10.0	10.0	10
93611	M12 x 1.50	14.0	10.0	10
93612	M16 x 1.50	17.0	10.0	10
93613	M20 x 1.50	21.0	10.0	10

Part no.	Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)
93614	M25 x 1.50	27.0	11.0	10
93615	M32 x 1.50	36.0	13.0	2
93616	M40 x 1.50	45.0	13.0	2
93617	M50 x 1.50	56.0	14.0	2

PG thread

Part no.	Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)
90730	PG 7	10.0	7.0	50
90731	PG 9	14.0	7.0	50
90732	PG 11	17.0	7.0	50
90733	PG 13.5	19.0	7.0	50
90734	PG 16	21.0	7.0	50

Part no.	Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)
90735	PG 21	27.0	10.0	25
90736	PG 29	36.0	10.0	25
90737	PG 36	45.0	10.0	25
90738	PG 48	56.0	10.0	10

PG thread - small packages

Part no.	Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)
93600	PG 7	10.0	7.0	10
93601	PG 9	14.0	7.0	10
93602	PG 11	17.0	7.0	10
93603	PG 13.5	19.0	7.0	10
93604	PG 16	21.0	7.0	10

Part no.	Size	Suitable for tube outer Ø mm	Thread length mm	Packaging unit (in pc.)
93605	PG 21	27.0	10.0	10
93606	PG 29	36.0	10.0	2
93607	PG 36	45.0	10.0	2
93608	PG 48	56.0	10.0	2