

Anaconda Sealtite® HTDL



TECHNICAL DATA

Protection tube

Temperature range	-45°C to +105°C short term up to +120°C
Protection class	IP 67

■ STRUCTURE

- Material: steel galvanized
- Outer sheath material: Polyvinylchlorid (PVC)
- reinforced, galvanised and spiral wound steel band
- with latched profile

- continuous copper conductor
- extruded plastic sheath

■ APPLICATION

- Good EMC properties.
Due to the complex construction method, the plastic sheath and internal tube flush together.

■ NOTES

- Suitable connection glands:
LT-straight, LT-elbow 45° and 90°
CV Compact straight, CV Compact elbow 45° and 90°

trade size inch	Inner Ø mm	Outer Ø mm, approx.	Weight kg, approx.	Packaging unit (in m)	black Part no.
3/8	12.6	17.8	0.40	60	98149
1/2	16.1	21.1	0.45	60	98150
3/4	21.1	26.4	0.65	45	98151
1	26.8	33.1	1.05	30	98152
1 1/4	35.4	41.8	1.20	15	98153
1 1/2	40.3	47.8	1.50	15	98154
2	51.6	59.9	2.30	15	98155