



## TECHNICAL DATA

### Protection tube

Temperature range	-45°C to +105°C short term up to +120°C
Protection class	IP 67

## ■ STRUCTURE

- Material: steel galvanized
- Outer sheath material: Polyvinylchlorid (PVC)
- reinforced, galvanised and spiral wound steel band
- with latched profile

- continuous copper conductor
- extruded plastic sheath

## ■ APPLICATION

- Good EMC properties.  
Due to the complex construction method, the plastic sheath and internal tube flush together.

## ■ NOTES

- Suitable connection glands:  
LT straight, LT angled, T&B straight, T&B angled.  
Up to 1 1/4" with copper conductor.

trade size inch	Inner Ø mm	Outer Ø mm, approx.	Weight kg, approx.	Packaging unit (in m)	black Part no.
3/8	12.6	17.8	0.40	60	<b>98149</b>
1/2	16.1	21.1	0.45	60	<b>98150</b>
3/4	21.1	26.4	0.65	45	<b>98151</b>
1	26.8	33.1	1.05	30	<b>98152</b>
1 1/4	35.4	41.8	1.20	15	<b>98153</b>
1 1/2	40.3	47.8	1.50	15	<b>98154</b>
2	51.6	59.9	2.30	15	<b>98155</b>