



TECHNICAL DATA

Polyolefin shrink tube 2:1

Temperature range -55°C to +125°C

■ PROPERTIES

- halogen-free
- cadmium-free

- lead-free

■ APPLICATION

- Machine and plant construction
- Automation technology
- Installation technology
- Control cabinet construction
- for repairing insulation
- for sealing electrical components

Inner Ø before shrink- age mm	Wall thickness mm	Inner Ø after shrinkage mm	Packaging unit (in m)	black Part no.
1.6	0.4	0.8	150.0	99551
2.4	0.5	1.2	150.0	99552
3.2	0.5	1.6	150.0	99553
4.8	0.5	2.4	75.0	99554
6.4	0.6	3.2	75.0	99555
9.5	0.6	4.8	75.0	99556
12.7	0.6	6.4	50.0	99557
16.0	0.6	8.0	50.0	99558
19.0	0.7	9.5	30.0	99559
25.4	0.8	12.7	30.0	99560
31.8	0.8	15.9	30.0	99561
38.0	1.0	19.0	30.0	99562
51.0	1.1	25.4	30.0	99563