


HELU-S-RK-N

for high temperature applications



TECHNICAL DATA

Tubular cable lug

Flange shape Ring shape
 Connecting angle 180° (horizontal)
 Temperature range up to +500°C

STRUCTURE

- Material: Nickel
- uninsulated
- without Inspection hole

PROPERTIES

- for high temperature applications

NOTES

- Legend:
 Dimensions
 a - Diameter of stud hole
 b - Width of flange
 d - Inner diameter of wire receptable
 l - Length to centre of hole

Part no.	Cross-sec. mm ²	Stud hole (M)	ø Stud hole (a) in mm	Flange width (b) in mm	ø Wire receptable (d) in mm	Length (l) in mm	Wall thickness mm	Weight in kg/1000 pc.	Packaging unit (in pc.)
98267	0.50 - 1.00	4	4.3	7.0	1.6	13.5	0.8	0.8	100
98268	0.50 - 1.00	5	5.3	7.5	1.6	14.5	0.8	0.8	100
97805	1.50 - 2.50	4	4.3	7.0	2.3	14.0	0.8	1.1	100
97806	1.50 - 2.50	5	5.3	8.5	2.3	15.5	0.8	1.2	100
97807	1.50 - 2.50	6	6.4	9.5	2.3	17.0	0.8	1.3	100
98269	4.00 - 6.00	4	4.3	9.5	3.6	18.0	1	2.6	100
97808	4.00 - 6.00	5	5.3	10.0	3.6	18.5	1	2.75	100
97809	4.00 - 6.00	6	6.4	10.5	3.6	19.5	1	2.9	100
98270	10.00	5	5.3	10.8	4.5	20.5	1	3.8	100
98271	10.00	6	6.4	11.5	4.5	22.5	1	4.2	100
98272	16.00	5	5.5	12.8	5.5	22.5	1	4.4	100
98273	16.00	6	6.4	13.6	5.5	24.5	1	4.8	100
98274	16.00	8	8.5	15.7	5.5	26.5	1	5.4	100
98275	25.00	6	6.4	14.0	7.0	30.0	1.5	12.0	50
98276	25.00	8	8.4	16.0	7.0	32.0	1.5	13.2	50
98277	35.00	6	6.4	17.0	8.5	32.0	1.75	18.5	50
98278	35.00	8	8.4	17.0	8.5	34.0	1.75	20.0	50
98279	50.00	8	8.4	20.0	10.0	37.0	2	29.0	50
98280	50.00	10	10.5	20.0	10.0	39.0	2	31.0	50
98281	70.00	10	10.5	23.0	12.0	44.0	2.25	46.0	25
98282	70.00	12	13.0	23.0	12.0	46.0	2.25	46.6	25
98283	95.00	10	10.5	26.0	13.5	48.0	2.25	55.5	25
98284	95.00	12	13.0	26.0	13.5	49.0	2.25	56.0	25

08.01.2024 / We reserve the right to make technical changes; the imprint in the image is purely exemplary