

LAN Cable

Category 5e

HELUKAT® 200 CPR Dca

SF/UTP duplex






Cable structure

SF/UTP 2x(4x2xAWG 24/1) FRNC

Inner conductor Ø:	0,51 mm
Conductor material:	Copper, bare
Core insulation:	Foam-skin-PE
Core colours:	whbu/bu, whog/og, whgn/gn, whbn/bn
Separator:	-
Screen over stranding element:	-
Screen 1 over stranding:	Al-Foil
Screen 2 over stranding:	Cu braid
Outer sheath material:	FRNC
Cable dimensions:	app. 6,0 mm x 12,5 mm
Outer sheath colour:	Green similar to RAL 6018



Electrical data


Characteristic impedance:	100 Ohm ± 15 Ohm at 1 to 100 MHz 100 Ohm ± 20 Ohm at 101 to 200 MHz
Loop resistance:	185 Ohm/km max.
Mutual capacitance:	48 nF/km nom.
Rel. propagation velocity:	74 %

Typical values

Frequency	(MHz)	10	16	62,5	100	200
Attenuation	(dB/100m)	5,6	7,2	14,4	18,2	25,9
Next	(db)	62,0	59,0	50,0	46,0	40,0
ACR	(db)	56,4	51,8	35,6	27,8	14,6

Technical data

Weight:	app. 100 kg/km
bending radius, repeated:	52 mm
Operating temperature range min.:	-20°C
Operating temperature range max.:	+60°C
Caloric load, approx. value:	0,96 MJ/m
Copper weight:	56,00 kg/km



Norms

Acc. to ISO/IEC 11801, Acc. to EN 50173, Acc. to EIA/TIA 568-A, Category 5e, Flame-retardant acc. to IEC 60332-3, Smoke density acc. to IEC 61034, Halogen-free acc. to 60754-2, Corrosiveness acc. to EN50267-2-3

Application

HELUKAT®200 data cables are used in the tertiary, but also in the secondary level of a network. They are characterized by large performance reserves and outstanding performance. They can be used to implement services such as Gigabit Ethernet, Fast Ethernet, Ethernet, ATM155, FDDI, token ring 4/16 Mbit/s, or ISDN absolutely trouble-free. Likewise, the mechanical characteristics are perfectly suited for the application in tight cable channels and platforms due to their optimized construction.

Part no.

81123, SF/UTP 2x(4x2xAWG 24/1) FRNC (S-FTP)

Dimensions and specifications may be changed without prior notice.