


# HELU-S-RK-45-CU-UL



## TECHNICAL DATA

### Angled tubular cable lug

Flange shape	Ring shape
Connecting angle	45°
Temperature range	up to +120°C

## ■ STRUCTURE

- Material: copper acc. to DIN EN 13600
- Surface: galvanic tin plated

- uninsulated
- without Inspection hole

## ■ NOTES

- Recommended pressing method: WM pressing
- Legend:  
Dimensions  
a - Diameter of stud hole  
b - Width of flange  
d - Inner diameter of wire receptable

Part no.	Cross-sec. mm <sup>2</sup> , approx.	Stud hole (M)	ø Stud hole (a) in mm	Flange width (b) in mm	ø Wire receptable (d) in mm	Weight in kg/1000 pc.	Packaging unit (in pc.)
907597	10	5	5.3	12.0	4.5	5.5	100
907598	10	6	6.4	12.0	4.5	5.8	100
907599	10	8	8.4	15.0	4.5	6.5	100
907600	10	10	10.5	18.0	4.5	6.6	100
907601	16	5	5.3	12.0	5.5	9.5	100
907467	16	6	6.4	12.0	5.5	10.2	100
907468	16	8	8.4	15.0	5.5	11.7	100
907469	16	10	10.5	18.0	5.5	11.7	100
907470	25	6	6.4	15.0	7.0	13.9	100
907471	25	8	8.4	16.0	7.0	15.1	100
907472	25	10	10.5	18.0	7.0	16.6	100
907473	25	12	13.0	20.0	7.0	17.0	100
907474	35	6	6.4	17.0	8.5	21.7	50
907475	35	8	8.4	17.0	8.5	24.6	50
907476	35	10	10.5	20.0	8.5	23.4	50
907477	35	12	13.0	22.0	8.5	24.0	50
907478	50	6	6.4	20.0	10.0	29.4	50
907479	50	8	8.4	20.0	10.0	33.4	50
907480	50	10	10.5	20.0	10.0	36.5	50
907481	50	12	13.0	23.0	10.0	38.6	50
907482	70	8	8.4	24.0	12.0	49.0	25
907483	70	10	10.5	24.0	12.0	53.9	25
907484	70	12	13.0	24.0	12.0	53.4	25
907485	95	8	8.4	26.0	13.5	61.8	25
907486	95	10	10.5	26.0	13.5	62.0	25
907487	95	12	13.0	26.0	13.5	62.0	25
907488	95	16	17.0	28.0	13.5	68.0	25
907489	120	8	8.4	29.0	15.0	78.0	25
907490	120	10	10.5	29.0	15.0	89.0	25
907491	120	12	13.0	29.0	15.0	89.1	25
907492	120	16	17.0	30.0	15.0	93.1	25

Continued on next page

# HELU-S-RK-45-CU-UL

Part no.	Cross-sec. mm <sup>2</sup> , approx.	Stud hole (M)	∅ Stud hole (a) in mm	Flange width (b) in mm	∅ Wire receptable (d) in mm	Weight in kg/1000 pc.	Packaging unit (in pc.)
907493	150	8	8.4	31.0	16.8	113.1	25
907494	150	10	10.5	31.0	16.8	98.0	25
907495	150	12	13.0	31.0	16.8	109.1	25
907496	150	16	17.0	31.0	16.8	101.2	25
907497	150	20	21.0	35.0	16.8	101.2	25
907498	185	10	10.5	35.0	19.0	123.5	20
907499	185	12	13.0	35.0	19.0	122.4	20
907500	185	16	17.0	35.0	19.0	128.4	20
907501	185	20	21.0	35.0	19.0	139.9	20
907502	240	12	13.0	38.0	21.0	154.6	15
907503	240	16	17.0	38.0	21.0	165.1	15
907504	240	20	21.0	38.0	21.0	170.4	15
907505	300	12	13.0	43.0	24.0	257.0	15
907506	300	16	17.0	43.0	24.0	256.8	15
907507	300	20	21.0	43.0	24.0	241.0	15