



BHA / BHB / BHC eye type



TECHNICAL DATA

Crimp cable lug acc. to DIN EN 45545-2

Flange shape	Ring shape
Temperature range	-20°C to +115°C short term up to +130°C

■ STRUCTURE

- Material: copper
- Surface: galvanic tin plated
- Insulation: Polycarbonat (PC)
- partially insulated
- Flammability acc. to UL 94 (V0)

■ APPLICATION

- Polycarbonate-insulated connection material on tape has been developed as a cost-effective solution for medium and large pre-fabricated cables.

■ NOTES

- Roll diameter: 450mm
Inner diameter of inclusion: 27mm
Blade terminal / blade receptacle / pin-type cable lug on tape on request.
- Legend:
Dimensions
a - Diameter of stud hole
b - Width of flange
d - Inner diameter of wire receptacle
l - Length to centre of hole

Part no.	Type	Colour	Cross-sec. mm², approx.	Packaging unit (in pc.)
93740	BHA 3	red	0.25 - 1.50	2000
93741	BHA 35	red	0.25 - 1.50	2000
93742	BHA 4	red	0.25 - 1.50	2000
93743	BHA 5	red	0.25 - 1.50	2000
93744	BHA 6	red	0.25 - 1.50	2000
93745	BHB 3	blue	1.50 - 2.50	1750
93746	BHB 4	blue	1.50 - 2.50	1750

Part no.	Type	Colour	Cross-sec. mm², approx.	Packaging unit (in pc.)
93747	BHB 5	blue	1.50 - 2.50	1750
93748	BHB 6	blue	1.50 - 2.50	1750
93749	BHB 8	blue	1.50 - 2.50	1750
93750	BHC 4	yellow	4.00 - 6.00	1250
93751	BHC 5	yellow	4.00 - 6.00	1250
93752	BHC 6	yellow	4.00 - 6.00	1250
93753	BHC 8	yellow	4.00 - 6.00	1250