

Certificate of compliance

with the order 2.1 according to EN 10 204

TOPFLEX[®]-EMV-3-PLUS-2YSLCY-J

We confirm that the above mentioned **Motor connection cable for frequency converters** is produced **in alignment with DIN VDE 0250** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range flexible +5°C to +70°C
fixed -40°C to +70°C

Nominal voltage AC U₀/U 600/1000 V

TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2
electromagnetic compatibility acc. to DIN VDE 0875-11 / DIN EN 55011
minimum cross-section of 0.75 mm² meets requirements acc. to DIN EN 60204-1
certifications and approvals:
EAC

PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
04.01.2024

Date of expiration
31.12.2025

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstrasse 10
71282 Hemmingen
Germany