

Certificate of compliance

with the order 2.1 according to EN 10 204

H07ZZ-F

We confirm that the above mentioned **Control and connection cable** is produced **acc. to DIN VDE 0285-525-3-21 / DIN EN 50525-3-21** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible -5°C to +80°C fixed -20°C to +80°C
Permissible operating temperature of the conductor	+90°C
Nominal voltage	flexible AC U ₀ /U 450/750 V

TESTS

halogen-free acc. to DIN VDE 0285-525-1 / DIN EN 50525-1 Appendix B
corrosiveness of combustion gases acc. to DIN VDE 0482-754-2 / DIN EN 60754-2 / IEC 60754-2
flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2
bundle fire test acc. to DIN VDE 0482-332-3-24 / DIN EN 60332-3-24 / IEC 60332-3-24
smoke density acc. to DIN VDE 0482-1034-1+2 / DIN EN 61034-1+2 / IEC 61034-1+2
ozone-resistant acc. to DIN VDE 0473-811-403 / DIN EN 60811-403
certifications and approvals:
HAR
EAC



Product conforms with Low-Voltage Directive 2014/35/EU

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
12.12.2024

Date of expiration
31.12.2026

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstrasse 10
71282 Hemmingen
Germany