

HELU KABEL GmbH  
Headquarters  
Dieselstraße 8-12  
71282 Hemmingen  
Germany

P +49 7150 9209-0  
F +49 7150 81786  
techsupport@helukabel.de  
helukabel.com

Helukabel GmbH • Dieselstraße 8-12 • 71282 Hemmingen • Germany

**Certificate of compliance  
with the order 2.1 according to EN 10 204**

Telephone, Name	Date	Effective date
-712, C. Dettmer	01.06.2021	31.07.2022

**TRAYCONTROL® 600-C**

We confirm that the above mentioned, screened PVC cables, NFPA 79, are produced according to UL-Std. 1277 and UL-Std. 2277.

- **Temperature range**
  - flexing + 5°C to + 50°C
  - fixed installation - 25°C to + 90°C
- **Nominal voltage**
  - TC, MTW, CIC, AWM 600V
  - WTTC 1000V

**Tests**

- Flame retardant acc. to CSA FT4

**Approvals:**

- **UL:**
  - TC-ER, 90 °C Dry / Wet (TC), PLTC (18 - 12 AWG),
  - ITC-ER (18 - 12 AWG), MTW, WTTC, SUN RES, DIR BUR,
  - OIL RES I/II, Class 1 Div. 2 per NEC Art. 501
- **CSA:**
  - c(UL) CIC-TC FT4, CSA AWM I/II A/B FT4.

The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers.

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature



Austria • Belgium • Brazil • Bulgaria • Canada • China • Czech Republic • Denmark • Finland • France • Germany • Hungary • India • Indonesia • Italy • Malaysia • Mexico • Myanmar • Netherlands  
Peru • Poland • Portugal • Romania • Russia • Singapore • South Africa • South Korea • Spain • Sweden • Switzerland • United Arab Emirates • United Kingdom • USA • Thailand • Turkey • Vietnam