

Certificate of compliance

with the order 2.1 according to EN 10 204

JZ-604 TC TRAY CABLE / OZ-604 TC TRAY CABLE

We confirm that the above mentioned **PVC control and connection cable** is produced **acc. to UL-Std. 1277 (TC), UL-Std. 1063 (MTW), UL-Std. 2277 (WTTTC), UL-Std. 758 (AWM) Style 2587, CSA-Std. C22.2 No. 210 - AWM I/II A/B** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible -5°C to +90°C fixed -40°C to +90°C
Nominal voltage	UL (AWM) AC 600 V UL (TC) AC 600 V UL (WTTTC) AC 1000 V UL (MTW) AC 600 V

TESTS

flame-retardant acc. to CSA FT4
oil-resistant acc. to UL Oil Res I, UL Oil Res II
90°C DRY/ 75°C WET acc. to UL Std. 1277 No. 9
Cold Bend Test acc. to UL Std. 1277 No. 17
Impact Test (-ER) acc. to UL Std. 1277 No. 23
Crushing Test (-ER) acc. to UL Std. 1277 No. 24
certifications and approvals:
EAC
Part numbers with protective conductor (GN-YE): for Class 1 Div. 2 explosive environments acc. to NEC Art. 501

PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
25.03.2024

Date of expiration
31.12.2025

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstraße 10
71282 Hemmingen
Germany