

Certificate of compliance

with the order 2.1 according to EN 10 204

SOLARFLEX®-X H1Z2Z2-K

We confirm that the above mentioned **Cross-linked single core cable** is produced **acc. to DIN VDE 0283-618 / DIN EN 50618** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible -25°C to +60°C fixed -40°C to +90°C
Permissible operating temperature of the conductor	+120°C
Short circuit temperature at the conductor	+250°C (Short circuit duration max. 5 s)
Nominal voltage	AC U ₀ /U 1000/1000 V DC U ₀ /U 1500/1500 V

TESTS

halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1
flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2
smoke density acc. to DIN VDE 0482-1034-1+2 / DIN EN 61034-1+2 / IEC 61034-1+2
UV-resistant acc. to DIN VDE 0283-618 / DIN EN 50618 Appendix E
ozone-resistant acc. to DIN VDE 0283-618 / DIN EN 50618
weather-resistant acc. to DIN VDE 0283-618 / DIN EN 50618 Appendix E
water-resistant acc. to DIN VDE 0285-525-2-21 / DIN EN 50525-2-21 Appendix E
Current carrying capacity acc. to DIN VDE 0283-618 / DIN EN 50618
Short-circuit and earth-fault proof acc. to DIN VDE 0100-520 / HD 60364-5-52
DC Voltage resistance of the insulation acc. to DIN VDE 0283-618 / DIN EN 50618 Tab. 2
certifications and approvals:
EAC
TÜV Rheinland



Product conforms with Low-Voltage Directive 2014/35/EU

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
03.03.2026

Date of expiration
31.12.2027

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstrasse 10
71282 Hemmingen
Germany