

Certificate of compliance

with the order 2.1 according to EN 10 204

H01N2-D

We confirm that the above mentioned **Arc welding cable** is produced **acc. to DIN VDE 0285-525-2-81 / DIN EN 50525-2-81** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible -20°C to +85°C fixed -35°C to +85°C
Permissible operating temperature of the conductor	+85°C
Nominal voltage	AC U ₀ /U 100/100 V

TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2

oil-resistant acc. to DIN VDE 0473-811-404 / DIN EN 60811-404 / IEC 60811-404

certifications and approvals:

HAR

EAC

PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
14.02.2025

Date of expiration
31.12.2027

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstrasse 10
71282 Hemmingen
Germany