

# Certificate of compliance

with the order 2.1 according to EN 10 204

## DATAFLAMM®-C

We confirm that the above mentioned **Data cable** is produced acc. to company specifications and tested according to DIN EN 50395, DIN EN 50396.

### TECHNICAL DATA

<b>Temperature range</b>	flexible +5°C to +70°C fixed -40°C to +70°C
<b>Peak operating voltage</b>	0.14 mm <sup>2</sup> : 350 V 0.25 - 0.75 mm <sup>2</sup> : 500 V (not for high power current installation purposes)

### TESTS

halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1  
corrosiveness of combustion gases acc. to DIN VDE 0482-754-2 / DIN EN 60754-2 / IEC 60754-2  
flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2 (outer sheath)  
certifications and approvals:  
EAC

### PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature

**Date of issue**  
18.12.2023

**Date of expiration**  
31.12.2025

**Point of Contact**  
Christian Dettmer  
Tel. +49 7150 9209-712  
techsupport@helukabel.de  
helukabel.com

**HELU KABEL GmbH**  
Headquarters  
Schloßhaldenstr. 10  
71282 Hemmingen  
Germany