

Certificate of compliance

with the order 2.1 according to EN 10 204

SiHF/GL-P

We confirm that the above mentioned **Silicone control and connection cable** is produced **in alignment with DIN VDE 0250-1, DIN VDE 0285-525-2-83 / DIN EN 50525-2-83** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range

flexible +5°C to +180°C

fixed -60°C to +180°C

Permissible operating temperature of the conductor

+180°C

Nominal voltage

AC U₀/U 300/500 V

TESTS

halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1

corrosiveness of combustion gases acc. to DIN VDE 0482-754-2 / DIN EN 60754-2 / IEC 60754-2

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2

certifications and approvals:

EAC



Product conforms with Low-Voltage Directive 2014/35/EU

HELUX KABEL GmbH

Technical Department

This document is valid without signature

Date of issue

27.03.2026

Date of expiration

31.12.2028

Point of Contact

Christian Dettmer

Tel. +49 7150 9209-712

techsupport@helukabel.de

helu.com

HELUX KABEL GmbH

Headquarters

Schloßhaldenstraße 10

71282 Hemmingen

Germany