

# Certificate of compliance

with the order 2.1 according to EN 10 204

## FIVENORM H07V2-K / 07V2-K / H07V-K / 07V-K

We confirm that the above mentioned **PVC single core** is produced **acc. to UL-Std. 758 (AWM) Style 10269, UL-Std. 1063 (MTW), CSA-Std. C22.2 No. 210 - AWM I A/B, 1.5 – 120 mm<sup>2</sup>: CSA-Std. C22.2 No. 127 - TEW** and tested according to DIN EN 50395, DIN EN 50396.

### TECHNICAL DATA

<b>Temperature range</b>	flexible +5°C to +90°C
	fixed -40°C to +90°C
<b>Nominal voltage</b>	UL (AWM) -40°C to +105°C
	UL (MTW) -40°C to +90°C
	CSA (TEW) -40°C to +105°C
	AC U <sub>0</sub> /U 450/750 V
	UL (AWM) AC 1000 V
	UL (AWM) DC 1250 V
	UL (MTW) AC 600 V
	CSA (TEW) AC 600 V

### TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, UL VW-1, CSA FT1  
certifications and approvals:  
FIVENORM H07V-K - FIVENORM H07V2-K: HAR  
FIVENORM H07V2-K: EAC

### PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature

**Date of issue**  
05.07.2023

**Date of expiration**  
31.12.2024

**Point of Contact**  
Christian Dettmer  
Tel. +49 7150 9209-712  
techsupport@helukabel.de  
helukabel.com

**HELU KABEL GmbH**  
Headquarters  
Schloßhaldenstraße 10  
71282 Hemmingen  
Germany