

Certificate of compliance

with the order 2.1 according to EN 10 204

HELUPOWER® H07RN-F LS0H

We confirm that the above mentioned **Rubber connection cable** is produced **acc. to DIN VDE 0285-525-2-21 / DIN EN 50525-2-21** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible -40°C to +90°C fixed -50°C to +90°C
Permissible operating temperature of the conductor	+90°C
Nominal voltage	AC U ₀ /U 450/750 V

TESTS

halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1
corrosiveness of combustion gases acc. to DIN VDE 0482-754-2 / DIN EN 60754-2 / IEC 60754-2
flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2
smoke density acc. to DIN VDE 0482-1034-1+2 / DIN EN 61034-1+2 / IEC 61034-1+2
oil-resistant acc. to DIN VDE 0473-811-404 / DIN EN 60811-404 / IEC 60811-404
ozone-resistant acc. to DIN VDE 0473-811-403 / DIN EN 60811-403
certifications and approvals:
HAR
EAC



Product conforms with Low-Voltage Directive 2014/35/EU

HELUX KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
27.03.2026

Date of expiration
31.12.2028

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helu.com

HELUX KABEL GmbH
Headquarters
Schloßhaldenstrasse 10
71282 Hemmingen
Germany