

Certificate of compliance

with the order 2.1 according to EN 10 204

DATAFLAMM®

We confirm that the above mentioned **Data cable** is produced acc. to company specifications and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible +5°C to +70°C fixed -40°C to +70°C
Peak operating voltage	0.14 mm ² : 350 V 0.25 - 0.75 mm ² : 500 V (not for high power current installation purposes)

TESTS

halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1
corrosiveness of combustion gases acc. to DIN VDE 0482-754-2 / DIN EN 60754-2 / IEC 60754-2
flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2 (outer sheath)
certifications and approvals:
EAC

PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
26.03.2026

Date of expiration
31.12.2028

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helu.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstraße 10
71282 Hemmingen
Germany