

Certificate of compliance

with the order 2.1 according to EN 10 204

HELUTHERM® 145 MULTI

We confirm that the above mentioned **Control and connection cable** is produced acc. to company specifications and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible -35°C to +120°C fixed -55°C to +145°C
Nominal voltage	0.25 - 1 mm ² : AC U ₀ /U 300/500 V 1.5 - 95 mm ² : AC U ₀ /U 450/750 V 1.5 - 95 mm ² : fixed and protected installation AC U ₀ /U 600/1000 V

TESTS

halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1
corrosiveness of combustion gases acc. to DIN VDE 0482-754-2 / DIN EN 60754-2 / IEC 60754-2
flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2
bundle fire test acc. to DIN VDE 0482-332-3-22 / DIN EN 60332-3-22 / IEC 60332-3-22
smoke density acc. to DIN VDE 0482-1034-1+2 / DIN EN 61034-1+2 / IEC 61034-1+2
oil-resistant acc. to DIN VDE 0473-811-404 / DIN EN 60811-404 / IEC 60811-404, IRM 902 4h at +70°C
UV-resistant acc. to DIN EN ISO 4892-2
weather-resistant acc. to DIN EN ISO 4892-2
certifications and approvals:
EAC
0.5 - 95 mm²: DNV

PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

HELUX KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
27.03.2026

Date of expiration
31.12.2028

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helu.com

HELUX KABEL GmbH
Headquarters
Schloßhaldenstrasse 10
71282 Hemmingen
Germany