

Certificate of compliance

with the order 2.1 according to EN 10 204

FIVENORM H05V2-K

We confirm that the above mentioned **PVC single core** is produced **acc. to UL-Std. 758 (AWM) Style 10269, UL-Std. 1063 (MTW), CSA-Std. C22.2 No. 127 – TEW, CSA-Std. C22.2 No. 210 - AWM I A/B, DIN VDE 0285-525-2-31 / DIN EN 50525-2-31** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible +5°C to +90°C
	fixed -40°C to +90°C
Nominal voltage	UL (AWM) -40°C to +105°C
	UL (MTW) -40°C to +90°C
	CSA (TEW) -40°C to +105°C
	AC U ₀ /U 300/500 V
	UL (AWM) AC 1000 V
	UL (AWM) DC 1250 V
	UL (MTW) AC 600 V
	CSA (TEW) AC 600 V

TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, UL VW-1, CSA FT1

certifications and approvals:

HAR

EAC

PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

HELUX KABEL GmbH

Technical Department

This document is valid without signature

Date of issue

21.07.2026

Date of expiration

31.12.2028

Point of Contact

Christian Dettmer

Tel. +49 7150 9209-712

techsupport@helukabel.de

helu.com

HELUX KABEL GmbH

Headquarters

Schloßhaldenstraße 10

71282 Hemmingen

Germany