

Certificate of compliance

with the order 2.1 according to EN 10 204

HELUWIND® WK 110-TORSION-MULTI

We confirm that the above mentioned **Torsion resistant cable** is produced acc. to company specifications and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range

flexible -40°C to +90°C

fixed -40°C to +90°C

Permissible operating temperature of the conductor

+90°C

Nominal voltage

VDE AC U₀/U 600/1000 V

TESTS

halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1

corrosiveness of combustion gases acc. to DIN VDE 0482-754-2 / DIN EN 60754-2 / IEC 60754-2

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2

smoke density acc. to DIN VDE 0482-1034-1+2 / DIN EN 61034-1+2 / IEC 61034-1+2

oil-resistant acc. to DIN VDE 0473-811-404 / DIN EN 60811-404 / IEC 60811-404



Product conforms with Low-Voltage Directive 2014/35/EU

HELUX KABEL GmbH

Technical Department

This document is valid without signature

Date of issue

19.06.2026

Date of expiration

31.12.2028

Point of Contact

Christian Dettmer

Tel. +49 7150 9209-712

techsupport@helukabel.de

helu.com

HELUX KABEL GmbH

Headquarters

Schloßhaldenstrasse 10

71282 Hemmingen

Germany